

Bitzer 4G-30.2Y-40P (x2)

Specifications

| Brand | Bitzer |
|--------------------------|------------------------|
| Туре | 4G-30.2Y-40P (x2) |
| Refrigerant | Freon |
| kW at 0ºC/+40ºC | 137,1 |
| kW at -5ºC/+40ºC | 114,0 |
| kW at -10ºC/+40ºC | 93,9 |
| kW at -20ºC/+40ºC | 61,4 |
| kW at -30ºC/+40ºC | 37,2 |
| kW at -40ºC/+40ºC | 19,7 |
| On steel base frame | ✓ |
| Pressure safety switches | 1 |
| Hp/Lp/Op | |
| Pressure gauges | ✓ |
| Hp/Lp/Op | |
| Liquid receiver | ✓ |
| Liquid receiver ltr. | 112 |
| Suction accumulator | ✓ |
| Oil separator | ✓ |
| Oil level system AC&R | ✓ |
| Liquid line filter drier | ✓ |
| Sight Glass | ✓ |
| Solenoid Valve | ✓ |
| Control panel | ✓ |
| m3 / h | 169,2 at 50 Hz & 204,2 |
| | m³/h at 60 Hz |
| Remarks | Y.o.b. 2010 |
| Package / Rack | 1 |





| | | Used Bitzer 4G-30.2Y-40P (x2) |
|-------|-------------------|-------------------------------|
| Stock | 1 | Description |
| | (LxWxH) | Description |
| Sizes | 3150x1370x2200 mm | |

Used Bitzer 4G-30.2Y-40P semihermetic reciprocating compressor rack on Freon. Complete with a suction accumulator, Bitzer FS1122 liquid receiver with a volume of 112 liter, oil separator, oil reservoir, 2 Yaskawa Varispeed, liquid line filter driers and a control cabinet. *Why choose for HOSBV? Were not only the largest used refrigeration specialist in Europe, but also, we deliver all equipment including an extensive test, warranty and industrial cleaning. *Optional we can also perform a new paint job and arrange the logistics.























| Réservoir es | t sous pression. | | 378008 | 1. 1. 1. 1. 1. 1. 1. 1. 1. 1. 1. 1. 1. 1 | | | |
|---|------------------|------------------|---------|--|------------------------|--|--|
| BITZER KÜHLMASCHINENBAU GMBH Made in E.C. | | | | | | | |
| SAK: 1178702382 Volumen Min/Max Temp. Baujahr 2010 Max.zuläss.Druck | Min/Max Temp. | Kältemittel 2 | | | al and a second second | | |
| | | v [| 112 | L | | | |
| | | TS | -10/120 | °C | - | | |
| | Max.zuläss.Druck | PS _ | 33 | bar | | | |
| 37804201 (E 0036 | | | | | | | |
| | | | | | | | |
| | | | | San test | J. | | |



















